

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	04/25/2023	DFRISIELLO	GUTTADAURO

D

D

C


C

B

B


A

A



NEMA 5/15P  
HOSPITAL GRADE  
BLACK

C19  
IEC60320  
BLACK



ANTI-MICROBIAL SJTOW3X14AWG  
105° C, BLACK


ITEM NUMBER	LENGTH, FT [mm]	TOLERANCE
AMHN515C19-15-3F	3.0 [915.0]	± .79 [20.0]
AMHN515C19-15-6F	6.0 [1830.0]	± .79 [20.0]
AMHN515C19-15-10F	10.0 [3050.0]	± .79 [20.0]

NOTES:

UL FILE: E234956  
RATING: 15A/250V

- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:  
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0  ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]      FRACTIONS ± 1/32 .XX = ± .02 [5]      ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS	DATE	 an INFINITI® brand	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	DRAWN BY DFRISIELLO	04/25/2023			
	CHECKED BY ELAMOTT	04/25/2023	CATEGORY	POWER CORD	
	APPROVED BY GUTTADAURO	04/25/2023	PRODUCT DESCRIPTION	HG N5-15P to C19, Antimicrobe Jkt, 15 A	
THIRD-ANGLE PROJECTION	COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321	ITEM NO. AMHN515C19-15	REV. A
		SCALE: NONE	CAD FILE: AMHN515C19-15.SLDDRW		SHEET 1 OF 1