

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	04/20/2023	DFRISIELLO	GUTTADAURO

D

C

B

A

D

C

B

A

NEMA 5/15P
HOSPITAL GRADE
BLACK


NEMA 5/15R
BLACK

NOTES:


UL FILE: E234956
RATING: 10A/125V

- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)



ITEM NUMBER	LENGTH, FT [mm]	TOLERANCE
AMHN515N515-10-3F	3.0 [915.0]	± .79 [20.0]
AMHN515N515-10-6F	6.0 [1830.0]	± .79 [20.0]
AMHN515N515-10-10F	10.0 [3050.0]	± .79 [20.0]

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		L-com™ an INFINITI® brand 50 High Street, West Mill, North Andover, MA 01845 USA Phone: 1.800.341.5266 1.978.682.6936	
OVERALL CABLE LENGTH TOLERANCE:		DRAWN BY		04/20/2023			
≤12 [305] = +1 [25] / -0		CHECKED BY		04/20/2023			
>12 [305] ≤60 [1524] = +2 [51] / -0		APPROVED BY		04/20/2023			
>60 [1524] ≤120 [3048] = +4 [102] / -0		GUTTADAURO				CATEGORY	
>120 [3048] ≤300 [7620] = +6 [152] / -0						POWER CORD	
>300 [7620] = +5% / -0						PRODUCT DESCRIPTION	
ALL OTHER DIMENSIONAL TOLERANCES:		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY				HG N5-15P to N5-15R, Antimicrobe Jkt, 10 A	
.X = ± .2 [5]		FRACTIONS				SIZE	
.XX = ± .02 [.5]		1/32				CAGE CODE	
.XXX = ± .005 [.13]		ANGLES ± 1°				ITEM NO.	
THIRD-ANGLE PROJECTION		COLOR VARIATIONS MAY OCCUR				AMHN515N515-10	
						REV.	
						SCALE: NONE	
						CAD FILE: AMHN515N515-10.SLDDRW	
						SHEET 1 OF 1	