



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	04/20/2023	DFRISIELLO	GUTTADAURO



NEMA 5/15P
HOSPITAL GRADE
BLACK

NEMA 5/15R
BLACK



ANTI-MICROBIAL SJTOW3X14AWG
105° C, BLACK


ITEM NUMBER	LENGTH, FT [mm]	TOLERANCE
AMHN515N515-15-3F	3.0 [915.0]	± .79 [20.0]
AMHN515N515-15-6F	6.0 [1830.0]	± .79 [20.0]
AMHN515N515-15-10F	10.0 [3050.0]	± .79 [20.0]

NOTES:

UL FILE: E234956
RATING: 15A/250V

- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS	DATE	L-com™ an INFINITI® brand		50 High Street, West Mill, North Andover, MA 01845 USA Phone: 1.800.341.5266 1.978.682.6936	
	DRAWN BY DFRISIELLO	04/20/2023				
	CHECKED BY ELAMOTT	04/20/2023	CATEGORY POWER CORD			
	APPROVED BY GUTTADAURO	04/20/2023				
THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION HG N5-15P to N5-15R, Antimicrobe Jkt, 15 A			
	COLOR VARIATIONS MAY OCCUR		SIZE A	CAGE CODE 43321	ITEM NO. AMHN515N515-15	REV A
		SCALE: NONE			CAD FILE: AMHN515N515-15.SLDDRW	SHEET 1 OF 1