


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/23/2007	KBURGER
B	-	11/23/2007	KBURGER
C	ECN 11129 UPDATE PER VENDOR	05/13/2021	SELLIS

PART	MATERIAL	FINISH
BODY	BRASS	NICKEL
PIN	BRASS	GOLD
FERRULE	BRASS	NICKEL
INSULATOR	PTFE	NATURAL
GASKET	SI-RUBBER	ORANGE



NOTES:

ELECTRICAL:



1. IMPEDANCE: 50 OHM
2. FREQUENCY RANGE: DC~11GHz
3. VOLTAGE RATING: 1500 VOLTS PEAK
4. DIELECTRIC WITHSTANDING VOLTAGE: 2500 VOLTS RMS
5. INSERTION LOSS: .20 dB MAX.

MISCILANEOUS:

1. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0	DRAWN BY BPUCHASKI	
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	CHECKED BY DFRISIELLO	05/13/2021	CATEGORY COAXIAL
	APPROVED BY SELLIS	05/13/2021	
THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A
SCALE: NONE		CAGE CODE 43321	ITEM NO. ANM-1304
SHEET 1 OF 1		CAD FILE: ANM-1304.SLDRW	