




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISION					
ZONE	REV.	DESCRIPTION	DATE	CHANGED BY	APPROVED BY
	A	INITIAL RELEASE	06/22/2023	BPUCHASKI	PHOSPODAR



MINI DISPLAYPORT 1.4 TO
DISPLAYPORT 1.4 ADAPTER
MALE CONNECTOR
WITH LATCHES



MINI DISPLAYPORT 1.4 TO
DISPLAYPORT 1.4 ADAPTER
MALE CONNECTOR
WITH LATCHES




HYBRID CABLE 4X FIBER AND
COPPER WIRE
JACKET: PVC, BLACK: NOM. DIA. .19[4.8]

NOTES:

1. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS .XX = ± .02 [.5] ± 1/32 .XXX = ± .005 [.13] ANGLES ± 1° THIRD-ANGLE PROJECTION 	APPROVALS	DATE	 an INFINITI® brand		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936		
	DRAWN BY BPUCHASKI	06/22/2023					
	CHECKED BY JJOHNSTON	06/22/2023	CATEGORY				
	APPROVED BY PHOSPODAR	06/22/2023	FIBER OPTICS				
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			PRODUCT DESCRIPTION Mini DisplayPort 1.4 to Mini DisplayPort Active Optical Cable, 8K				
COLOR VARIATIONS MAY OCCUR			SIZE A	CAGE CODE 43321	ITEM NO. AOC-MDPMDP4K	REV. A	
			SCALE: NONE			CAD FILE: AOC-MDPMDP4K.SLDRW	SHEET 1 OF 1