


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	REV A DRAWING RELEASED	02/13/2019	DFRISIELLO

DESCRIPTION	MATERIAL	FINISH
BODY	BRASS	NICKEL PLATE
SLEEVE	BRASS	NICKEL PLATE
INSULATOR	PTFE	NATURAL
PIN	BRASS	GOLD PLATE
SHELL	BRASS	NICKEL PLATE



**ELECTRICAL:**

IMPEDANCE: 50 OHMS  
 FREQUENCY RANGE: DC ~ 2.5 GHz  
 VOLTAGE RATING: 335 VOLTS RMS  
 DIELECTRIC WITHSTANDING VOLTAGE: 1000 VOLTS RMS  
 INSERTION LOSS: .15 dB MAX.

**NOTES:**

ALL DIMENSIONS ARE FOR REFERENCE ONLY.

ADAPTER SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ± .005 [1.27]	APPROVALS	DATE		50 HIGH STREET NORTH ANDOVER, MA 01845	
	DRAWN BY DFRISIELLO	02/13/2019		CATEGORY	COAXIAL
	CHECKED BY BPUCHASKI	02/13/2019		PRODUCT DESCRIPTION	ADP N-FEMALE TO MINI-UHF M
	APPROVED BY SELLIS	02/13/2019		SIZE <b>A</b> FSCM NO. <b>43321</b> DWG. NO. <b>AXA-NFMUM</b> REV. <b>A</b>	
PROJECTION	COLOR VARIATIONS MAY OCCUR	SCALE: NONE	CAD FILE: AXA-NFMUM.SLDDRW	SHEET 1 OF 1	