


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
A	RELEASED FOR PRODUCTION	01/04/02	MCCORMICK
B	ECN 3119: UPDATE DWG FORMAT	12/18/07	D.GRIFFIN



NOTES:

**MATERIAL:**  
 BODY: BRASS  
 DIELECTRIC: DELRIN  
 CONTACT: BRASS  
 COUPLING NUT: BRASS

**FINISH:**  
 BODY: NICKEL  
 CONTACT: GOLD  
 COUPLING NUT: NICKEL

**RoHS Compliant** ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] TOLERANCES TO BE: .X ±.1 [2.5] ANGLES ±2° .XX ±.01 [.25] .XXX ±.005 [.13] OVERALL CABLE LENGTH TOL: ≤ 60 [1524] +3 [76.2] / -0 > 60 [1524] +5% / -0%	APPROVALS	DATE	<b>L-com</b> CONNECTIVITY PRODUCTS 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY MCCORMICK	01/04/02		CATEGORY COAXIAL
	CHECKED BY D.PARHAM	01/04/02		PRODUCT DESCRIPTION F PLUG TO BNC JACK
	APPROVED BY R.CARRICK	01/04/02		SIZE <b>A</b> FSCM NO. <b>43321</b> DWG. NO. <b>BA120</b> REV. <b>B</b> SCALE: NONE   CAD FILE: BA120.SLDDRW   SHEET 1 OF 1
PROJ	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			