


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED FOR PRODUCTION	05/04/01	MCCORMICK
B	ECN 3131: UPDATE DWG FORMAT	12/28/07	D.GRIFFIN
C	ECN 3776: UPDATED DIMENSIONS, NEW FORMAT	12/31/08	D.FRISIELLO
D	ECN 7890: UPDATED FORMAT, PACKAGING, ROHS	4/1/15	D_DESJARDIN

DESCRIPTION	MATERIAL	FINISH
BODY	BRASS	NICKEL
CONTACT	BRASS	GOLD
DIELECTRIC	ACETAL	---



NOTES:

1. IMPEDANCE: 50 OHM
2. ADAPTER SHALL BE TESTED FOR CONTINUITY.
3. ADAPTER SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	DRAWN BY MCCORMICK	05/02/01		CATEGORY COAXIAL		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ±.005 [1.13]	CHECKED BY D.PARHAM	05/04/01	PRODUCT DESCRIPTION ADAPTER BNC F/BNC F, 50 OHM			
	APPROVED BY T.CLARK	05/04/01				
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. BA80	REV. D
REF	SCALE: NONE		CAD FILE: BA80.SLDDRW		SHEET 1 OF 1	