



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	05/12/2023	SREITER	GUTTADAURO



"HOSPITAL GRADE" DESIGNATION



NEMA HG 5-15P
PLUG



LENGTH

3.26
[82.8]

SJT 14AWG, BLACK
3-COND CORDAGE

3.25
[82.7]

C19 LOCKING
CONNECTOR



NOTES:

1. PLUG: HOSPITAL GRADE NEMA 5-15P, BLACK
2. CONNECTOR: C19 LOCKING, BLACK
3. CORDAGE: SJT3X14AWG, BLACK
4. FOR REFERENCE ONLY:
 - A. COLOR CODING OF CONDUCTORS: BLACK, WHITE, GREEN
 - B. APPROVALS: UL/CSA
 - C. RATING: 15A/125V
5. OPTIONAL LABELS MAY INCLUDE UL, CURRENT AND/OR WARNING.
6. CABLE ASSEMBLIES SHALL BE INDIVIDUALLY PACKAGED.

TABULATION BLOCK	
ITEM NO.	LENGTH ±.6 [15]
C19LHGN515P-15-3F	36.0 [914]
C19LHGN515P-15-6F	72.0 [1829]
C19LHGN515P-15-10F	120.0 [3048]

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5] FRACTIONS ± 1/32 .XX = ±.02 [.5] ANGLES ± 1° .XXX = ±.005 [.13]	APPROVALS DRAWN BY SREITER CHECKED BY DGUST APPROVED BY GUTTADAURO	DATE 05/12/2023 05/12/2023 05/12/2023	L-com™ an INFINITI® brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936		
	THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR		CATEGORY POWER PRODUCTS PRODUCT DESCRIPTION IEC LOCK C19 TO HG NEMA 5-15P, 15A, 125V	
		SIZE A	CAGE CODE 43321	ITEM NO. C19LHGN515P-15	REV. A
		SCALE: NONE	CAD FILE: C19LHGN515P-15-10F.SLDDRW	SHEET 1 OF 1	