


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/10/10	D.GRIFFIN





LENGTH CODE CHART		
CABLE# & LENGTH	LENGTH SYMBOL	EXAMPLES OF PART# USED
CA-NMNFEXX	WHERE XXX = LENGTH IN FEET	CA-NMNF010 (10 FEET)
CA-NMNFENXX	WHERE NXX = LENGTH IN INCHES	CA-NMNF016 (16 INCHES)
CA-NMNFEMXX	WHERE MXX = LENGTH IN METERS	CA-NMNF007 (7 METERS)
CA-NMNFEXMX	WHERE XMX = LENGTH IN DECIMAL METERS	CA-NMNF035 (3.5 METERS)

RoHS Compliant ✓

NOTES:

CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.

CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D.FRISIELLO	11/10/10	
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY K.BURGNER	11/10/10	CATEGORY COAXIAL
	APPROVED BY K.BURGNER	11/10/10	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION CA, CA-200 N-MALE/N-FEMALE	SIZE A FSCM NO. 43321 DWG. NO. CA-NMNF REV. A
COLOR VARIATIONS MAY OCCUR		SCALE: NONE	CAD FILE: CA-NMNF.SLDDRW
		SHEET 1 OF 1	