


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	9/29/10	D.GRIFFIN





LENGTH CODE CHART		
CABLE# & LENGTH	LENGTH SYMBOL	EXAMPLES OF PART# USED
CA-SBPSBJCXXX	WHERE XXX = LENGTH IN FEET	CA-SBPSBJC010 (10 FEET)
CA-SBPSBJCNXX	WHERE NXX = LENGTH IN INCHES	CA-SBPSBJC16 (16 INCHES)
CA-SBPSBJCMXX	WHERE MXX = LENGTH IN METERS	CA-SBPSBJCM07 (7 METERS)
CA-SBPSBJCXM	WHERE XM = LENGTH IN DECIMAL METERS	CA-SBPSBJC3M5 (3.5 METERS)

**RoHS Compliant** ✓

**NOTES:**

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPEC. PS-0031

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	DRAWN BY D. CASTRO	9/28/10				
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY J. RUST	9/28/10	CATEGORY <b>COAXIAL</b>			
	APPROVED BY K. BURGNER	9/28/10	PRODUCT DESCRIPTION <b>CA,CA-100 SMB PLUG / JACK</b>			
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>CA-SBPSBJCN</b>	REV. <b>A</b>
SCALE: NONE			CAD FILE: CA-SBPSBJCN.SLDDRW		SHEET 1 OF 1	