


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	7/23/10	D.GRIFFIN
B	ECN 5518: CN RELEASE	5/19/11	D. CASTRO





LENGTH CODE CHART		
CABLE# & LENGTH	LENGTH SYMBOL	EXAMPLES OF PART# USED
CA-SMRNMA $\underline{\text{XXX}}$	WHERE XXX = LENGTH IN FEET	CA-SMRNMA010 (10 FEET)
CA-SMRNMAN $\underline{\text{NXX}}$	WHERE NXX = LENGTH IN INCHES	CA-SMRNMAN16 (16 INCHES)
CA-SMRNMA $\underline{\text{MXX}}$	WHERE MXX = LENGTH IN METERS	CA-SMRNMA07 (7 METERS)
CA-SMRNMA $\underline{\text{XMX}}$	WHERE XMX = LENGTH IN DECIMAL METERS	CA-SMRNMA3M5 (3.5 METERS)

RoHS Compliant ✓

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D. CASTRO	7/22/10	
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY D. PARHAM	7/22/10	PRODUCT DESCRIPTION CA,195 SMA M RA/NM
	APPROVED BY K. BURGNER	7/22/10	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		COLOR VARIATIONS MAY OCCUR