



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/15/12	D.GRIFFIN



LENGTH CODE CHART		
CABLE# & LENGTH	LENGTH SYMBOL	EXAMPLES OF PART# USED
CA-SNPTFBCXXX	WHERE XXX = LENGTH IN FEET	CA-SNPTFBC010 (10 FEET)
CA-SNPTFBCNXX	WHERE NXX = LENGTH IN INCHES	CA-SNPTFBCN16 (16 INCHES)
CA-SNPTFBCMXX	WHERE MXX = LENGTH IN METERS	CA-SNPTFBCM07 (7 METERS)
CA-SNPTFBCXMX	WHERE XMX = LENGTH IN DECIMAL METERS	CA-SNPTFBC3M5 (3.5 METERS)



RECOMMENDED
PANEL CUTOUT

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL RECEIVE INSERTION LOSS TEST PER L-COM SPECIFICATIONS.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D. DESJARDIN	11/15/12		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY P. PESA	11/15/12	CATEGORY COAXIAL	
	APPROVED BY P. PESA	11/15/12	PRODUCT DESCRIPTION CA,SMA-NANO TO TNC-FEMALE BULK, 100 SERIES CABLE ASSY	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
			DWG. NO. CA-SNPTFBC	REV. A
			SCALE: NONE	CAD FILE: CA-SNPTFBC.SLDDRW
				SHEET 1 OF 1