


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

**RoHS Compliant** ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/31/12	D.GRIFFIN




"P1"  
USB SERIES A  
RIGHT ANGLE PLUG  
30 μINCHES  
GOLD PLATING

"P2"  
USB SERIES B  
DOWN ANGLE PLUG  
30 μINCHES  
GOLD PLATING

ONE 28AWG STRANDED TINNED COPPER TWISTED PAIR  
TWO 26AWG STRANDED TINNED COPPER CONDUCTORS  
OVERALL ALUMINIZED POLYESTER SHIELD WITH DRAIN WIRE  
PLUS TINNED COPPER BRAIDED SHIELD.  
PVC OUTER JACKET, GRAY (PANTONE 424C)

PART NUMBER	LENGTH	
	METERS	FEET
CA90RA-DB-03M	0.3	.98
CA90RA-DB-05M	0.5	1.64
CA90RA-DB-075M	0.75	2.46
CA90RA-DB-1M	1.0	3.28
CA90RA-DB-2M	2.0	6.56
CA90RA-DB-3M	3.0	9.84
CA90RA-DB-4M	4.0	13.12
CA90RA-DB-5M	5.0	16.41



- NOTES:
1. CABLE ASSEMBLY SHALL HAVE 360° SHIELD TERMINATION.
  2. CABLE ASSEMBLY SHALL MEET USB 2.0 REQUIREMENTS.
  3. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
  4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE	<b>L-com</b> Global Connectivity 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D. DESJARDIN	10/30/12	
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY D. FRISIELLO	10/30/12	PRODUCT DESCRIPTION <b>CA USB 90RT A/90DN B DX</b>
PROJECTION 	APPROVED BY S. SMITH	10/31/12	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		FSCM NO. <b>43321</b>
	COLOR VARIATIONS MAY OCCUR		DWG. NO. <b>CA90RA-DB</b>
			SCALE: NONE
			CAD FILE: CA90RA-DB.SLDDRW
			SHEET 1 OF 1