


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/1/12	D.GRIFFIN
B	ECN 6451: UPDATED NOTES & WIRING MAP. CHANGED EXPOSED CONN. DIM.	10/10/12	D. DESJARDIN



"P1"
5-PIN MINI B USB PLUG
RIGHT ANGLE DOWN
CONTACTS: 30 μINCHES
GOLD PLATING

"P2"
SERIES "A" USB PLUG
CONTACTS: 30 μINCHES
GOLD PLATING

MODEL NUMBER	LENGTH METERS [FEET]
CAA-90DMB5-03M	.3 [.98]
CAA-90DMB5-05M	.5 [1.64]
CAA-90DMB5-075M	.75 [2.46]
CAA-90DMB5-1M	1.0 [3.28]
CAA-90DMB5-2M	2.0 [6.56]
CAA-90DMB5-3M	3.0 [9.84]
CAA-90DMB5-5M	5.0 [16.41]



- NOTES:
1. CABLE ASSEMBLY SHALL HAVE 360° SHIELD TERMINATION.
 2. CABLE ASSEMBLY SHALL MEET USB 2.0 REQUIREMENTS.
 3. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D.FRISIELLO	5/17/11		CATEGORY
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY D.CASTRO	5/17/11	PRODUCT DESCRIPTION	
PROJECTION	APPROVED BY S.SMITH	5/17/11	CA USB STR A/90DN MB5	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
			DWG. NO. CAA-90DMB5	REV. B
			SCALE: NONE	CAD FILE: CAA-90DMB5.SLDRW
				SHEET 1 OF 1