

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 5268: ADDED LABEL WITH L-COM P/N TO NOTE 2	1/21/11	D. CASTRO
F	ECN 7476: UPDATED PACKAGING, ADDED ROHS, UPDATED FORMAT	6/9/14	D. CASTRO
-	-	-	-
-	-	-	-




"J1"

SERIAL ATA RECEPTACLE,
7 PIN CONNECTOR,
STRAIGHT W/ LATCH,
OVERMOLDED, COLOR: BLACK




"J2"

SERIAL ATA RECEPTACLE,
7 PIN CONNECTOR,
STRAIGHT W/ LATCH,
OVERMOLDED, COLOR: BLACK



WIRING DIAGRAM



PART #	LENGTH	
	INCHES	MILLIMETERS
CASATAL-8	8	203.2
CASATAL-12	12	304.8
CASATAL-16	16	406.4
CASATAL-18	18	457.2
CASATAL-24	24	609.6
CASATAL-36	36	914.4

NOTE:

1. EACH CABLE ASSEMBLY SHALL BE SUBJECTED TO A CONTINUITY TEST.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.



REGULATORY COMPLIANCE:
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [5.1] .XXX = ± .005 [1.3]	APPROVALS	DATE
	DRAWN BY E. STAUBLE	7/17/08
	CHECKED BY D. PARHAM	7/21/08
	APPROVED BY S. SMITH	7/21/08
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR

		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY HETEROGENOUS			
PRODUCT DESCRIPTION CBL,SATA W/LATCH STR/STR			
SIZE A	FSCM NO. 43321	DWG. NO. CASATAL-X	REV. F
SCALE: NONE		CAD FILE: CASATAL-X.SLDDRW	
			SHEET 1 OF 1