


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS |                 |         |           |
|-----------|-----------------|---------|-----------|
| REV       | DESCRIPTION     | DATE    | APPROVED  |
| A         | INITIAL RELEASE | 1/18/10 | D.GRIFFIN |
|           |                 |         |           |
|           |                 |         |           |



3 PIN FEMALE XLR CONNECTOR  
NICKEL PLATED CONTACTS

| WIRE MAP |       |
|----------|-------|
| "P1"     | "J1"  |
| TIP      | 2     |
| SLEEVE   | 3 & 1 |

| PART NUMBER | LENGTH |        | RING COLOR |
|-------------|--------|--------|------------|
|             | FEET   | METERS |            |
| CAXLR214-1  | 1.0    | .30    | BLACK      |
| CAXLR214-3  | 3.0    | .91    | BLACK      |
| CAXLR214-6  | 6.0    | 1.83   | BLACK      |
| CAXLR214-10 | 10.0   | 3.05   | BLACK      |
| CAXLR214-15 | 15.0   | 4.57   | BLACK      |
| CAXLR214-20 | 20.0   | 6.10   | BLACK      |
| CAXLR214-25 | 25.0   | 7.62   | BLACK      |

**RoHS Compliant** ✓

- NOTES:**
- CABLE SHALL BE TESTED FOR CONTINUITY.
  - CABLE SHALL BE PACKAGED IN ACCORDANCE WITH L-COM SPEC. PS-0031.

|   |  |                            |  |  |                      |                  |
|---|--|----------------------------|--|--|----------------------|------------------|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]<br>OVERALL CABLE LENGTH TOLERANCE:<br>≤12 [305] = +1 [25] / -0<br>>12 [305] ≤60 [1524] = +2 [51] / -0<br>>60 [1524] ≤120 [3048] = +4 [102] / -0<br>>120 [3048] ≤300 [7620] = +6 [152] / -0<br>>300 [7620] = +3% / -0% | APPROVALS  | DATE                       |  | 45 BEECHWOOD DRIVE<br>NORTH ANDOVER, MA<br>01845 |                      |                  |
|   | DRAWN BY<br>D. CASTRO                                    | 11/30/09                   |  |  |                      |                  |
| ALL OTHER DIMENSIONAL TOLERANCES:<br>.X = ± .2<br>.XX = ± .02<br>.XXX = ±.005   | CHECKED BY<br>D. PARHAM                                  | 12/1/09                    | CATEGORY<br>AUDIO                          |  |                      |                  |
|   | APPROVED BY<br>P. MCNEIL                                 | 12/2/09                    | PRODUCT DESCRIPTION<br>CA 1/4"/XLR-F AUDIO |  |                      |                  |
| PROJECTION<br>  | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY | COLOR VARIATIONS MAY OCCUR | SIZE<br><b>A</b>                           | FSCM NO.<br><b>43321</b>                         | DWG. NO.<br>CAXLR214 | REV.<br><b>A</b> |
|   |  |                            | SCALE: NONE                                | CAD FILE: CAXLR214.SLDDRW                        | SHEET 1 OF 1         |                  |