


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
C	ECN3027: CN RELEASE	10/02/07	D.PARHAM
D	ECN 6436: UPDATED LOGOS, DRAWING FORMAT, AND PACKAGING	9/28/12	D. DESJARDIN



PART NUMBER	LENGTH
	FEET [METERS]
CC59A-1HR2	1.0 [.30]
CC59A-1.5HR2	1.5 [.46]
CC59A-2HR2	2.0 [.61]
CC59A-2.5HR2	2.5 [.76]
CC59A-3HR2	3.0 [.91]
CC59A-4HR2	4.0 [1.22]
CC59A-5HR2	5.0 [1.52]
CC59A-7.5HR2	7.5 [2.28]
CC59A-10HR2	10.0 [3.05]

NOTES:

- CABLE SHALL BE TESTED FOR CONTINUITY.
- CABLE SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D.FRISIELLO	8/8/07		CATEGORY COAXIAL
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY J.KIEZULAS	8/8/07	PRODUCT DESCRIPTION RIGHT ANGLE BNC PLUG, RG59A	
PROJECTION 	APPROVED BY J.ROBERTS	8/8/07	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	
	COLOR VARIATIONS MAY OCCUR		SIZE A	FSCM NO. 43321
			DWG. NO. CC59A-HR2	REV. D
			SCALE: NONE	CAD FILE: CC59A-HR2.SLDDRW
				SHEET 1 OF 1