


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 4824: ADDED FFET TO CHART, ROHS STAMP, REVISED PACKAGING NOTE	6/10/10	D.FRISIELLO
F	ECN 6469: UPDATED DRAWING FORMAT AND LOGOS	10/17/12	D. DESJARDIN



MODEL P/N	LENGTH, FEET [MTR]
CC59A-RR-1	1.0 [.30]
CC59A-RR-3	3.0 [.91]
CC59A-RR-6	6.0 [1.83]
CC59A-RR-9	9.0 [2.74]
CC59A-RR-12	12.0 [3.66]

NOTES:

1. CABLE SHALL BE TESTED FOR CONTINUITY.
2. CABLE SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY MCCORMICK	06/28/01		CATEGORY
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY D.PARHAM	07/02/01	PRODUCT DESCRIPTION	
PROJECTION 	APPROVED BY ENG	07/02/01	CA RCA M/RCA M RG59A/U	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE A	FSCM NO. 43321
	COLOR VARIATIONS MAY OCCUR		DWG. NO. CC59A-RR	REV. F
			SCALE: NONE	CAD FILE: CC59A-RR.SLDDRW
				SHEET 1 OF 1