


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
C	ECN3028: CN RELEASE	10/02/07	D.PARHAM
D	ECN 6436: UPDATED LOGOS, PACKAGING, AND DRAWING FORMAT	9/28/12	D. DESJARDIN



PART NUMBER	LENGTH
	FEET [METERS]
CC59B-1HR	1.0 [.30]
CC59B-1.5HR	1.5 [.46]
CC59B-2HR	2.0 [.61]
CC59B-2.5HR	2.5 [.76]
CC59B-3HR	3.0 [.91]
CC59B-4HR	4.0 [1.22]
CC59B-5HR	5.0 [1.52]
CC59B-7.5HR	7.5 [2.28]
CC59B-10HR	10.0 [3.05]

NOTES:

- CABLE SHALL BE TESTED FOR CONTINUITY.
- CABLE SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVALS DRAWN BY D.FRISIELLO CHECKED BY J.KIEZULAS APPROVED BY J.ROBERTS	DATE 8/8/07 8/8/07 8/8/07	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	CATEGORY COAXIAL PRODUCT DESCRIPTION CA BNC M RA /BNC M RG59B/U		SCALE: NONE CAD FILE: CC59B-HR.SLDDRW
PROJECTION 	SIZE A	FSCM NO. 43321	DWG. NO. CC59B-HR	REV. D