


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
C	ECN3029: CN RELEASE	10/02/07	D.PARHAM
D	ECN 6436: UPDATED LOGOS, PACKAGING, AND DRAWING FORMAT	9/28/12	D. DESJARDIN



PART NUMBER	LENGTH
	FEET [METERS]
CC59B-1HR2	1.0 [.30]
CC59B-1.5HR2	1.5 [.46]
CC59B-2HR2	2.0 [.61]
CC59B-2.5HR2	2.5 [.76]
CC59B-3HR2	3.0 [.91]
CC59B-4HR2	4.0 [1.22]
CC59B-5HR2	5.0 [1.52]
CC59B-7.5HR2	7.5 [2.28]
CC59B-10HR2	10.0 [3.05]

NOTES:

- CABLE SHALL BE TESTED FOR CONTINUITY.
- CABLE SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

<p>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]</p> <p>OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%</p> <p>ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005</p> <p>PROJECTION </p>	<p>APPROVALS</p> <p>DRAWN BY D.FRISIELLO</p> <p>CHECKED BY J.KIEZULAS</p> <p>APPROVED BY J.ROBERTS</p>	<p>DATE</p> <p>8/8/07</p> <p>8/8/07</p> <p>8/8/07</p>	<p>45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845</p>	<p>CATEGORY</p> <p>COAXIAL</p>	
	<p>CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY</p>			<p>PRODUCT DESCRIPTION</p> <p>RIGHT ANGLE BNC PLUG, RG59B</p>	
	<p>COLOR VARIATIONS MAY OCCUR</p>	<p>SIZE</p> <p>A</p>	<p>FSCM NO.</p> <p>43321</p>	<p>DWG. NO.</p> <p>CC59B-HR2</p>	<p>REV.</p> <p>D</p>
	<p>SCALE: NONE</p>		<p>CAD FILE: CC59B-HR2.SLDDRW</p>	<p>SHEET 1 OF 1</p>	