



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	7/5/07	D.FRISIELLO
B	ECN #2945: ADDED GASKET TO BULKHEAD CONNECTOR.	8/14/07	D.FRISIELLO
C	ECN 8058: REVISED NOTES, FORMAT, ROHS	8/18/15	D.FRISIELLO



MODEL NUMBER	LENGTH FEET [METERS]
CC59B-MF-1	1.0 [.30]
CC59B-MF-3	3.0 [.91]
CC59B-MF-6	6.0 [1.83]
CC59B-MF-10	10.0 [3.05]
CC59B-MF-15	15.0 [4.57]
CC59B-MF-25	25.0 [7.62]
CC59B-MF-50	50.0 [15.24]



RECOMMENDED
PANEL OPENING



NOTES:

- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU (ROHS DIRECTIVE)



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D.FRISIELLO	6/28/07		CATEGORY AUDIO/VIDEO
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [51] .XXX = ±.005 [1.27]	CHECKED BY D.DOLCE	6/28/07	PRODUCT DESCRIPTION CA BNC M/BNC F BHD RG59B/U	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	APPROVED BY D.DOLCE	6/28/07	SCALE: NONE
	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. CC59B-MF
			CAD FILE: CC59B-MF.SLDDRW	SHEET 1 OF 1