

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS | | | |
|-----------|---------------------|----------|--------------|
| REV | DESCRIPTION | DATE | APPROVED |
| 1 | PRELIMINARY RELEASE | 09/17/07 | R.POLUBINSKI |
| A | INITIAL RELEASE | 09/18/07 | R.POLUBINSKI |
| | | | |
| | | | |




RG6 QUAD TYPE 75 OHM COAXIAL CABLE, 18 AWG COPPER COVERED STEEL CENTER CONDUCTOR, TWO ALUMINIZED FOIL SHIELDS AND TWO ALUMINUM BRAID SHIELDS. BLACK PVC NEC TYPE CL3 JACKET.

2X TYPE "F" PLUG BRASS NICKEL FINISH

| MODEL # | LENGTH | |
|----------|--------|--------|
| | FEET | METERS |
| CC6QF-05 | 0.5 | 0.152 |
| CC6QF-1 | 1.0 | 0.305 |
| CC6QF-3 | 3.0 | 0.915 |
| CC6QF-6 | 6.0 | 1.830 |
| CC6QF-9 | 9.0 | 2.743 |
| CC6QF-12 | 12.0 | 3.660 |
| CC6QF-25 | 25.0 | 7.620 |
| CC6QF-50 | 50.0 | 15.240 |

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]
 TOLERANCES TO BE:
 .X ±.1 [2.5] ANGLES ±2°
 .XX ±.01 [.25]
 .XXX ±.005 [.13]
 OVERALL CABLE LENGTH TOL:
 ≤ 60 [1524] +3 [76.2] / -0
 > 60 [1524] +5% / -0%



| APPROVALS | DATE |
|----------------------------|----------|
| DRAWN BY R.POLUBINSKI | 09/17/07 |
| CHECKED BY D.PARHAM | 09/17/07 |
| APPROVED BY D.FRISIELLO | 09/18/07 |

CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY

L-com 45 BEECHWOOD DRIVE
 CONNECTIVITY PRODUCTS NORTH ANDOVER, MA 01845

CATEGORY "F" TYPE CONNECTOR ASSEMBLIES

PRODUCT DESCRIPTION CA F M/F M RG6 QUAD SHIELD

| | | | |
|------------------|--------------------------|-----------------------------|------------------|
| SIZE A | FSCM NO. 43321 | DWG. NO. CC6QF-05 | REV. A |
| SCALE: NONE | | CAD FILE: CC6QF-05.SLDDRW | SHEET 1 OF 1 |