


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	01/29/04	MCCORMICK
B	ECN 3277: UPDATE DWG FORMAT	4/14/08	D.GRIFFIN
C	ECN 4635: CN RELEASE AND NEW FORMAT	3/25/10	D.FRISIELLO
D	ECN 4761: ADDED 100.0 FT LENGTH	5/20/10	D.FRISIELLO





MODEL NO.	LENGTH	
	FEET	METERS
CCF59B-1	1.0	.31
CCF59B-3	3.0	.91
CCF59B-6	6.0	1.83
CCF59B-9	9.0	2.74
CCF59B-12	12.0	3.66
CCF59B-25	25.0	7.62
CCF59B-50	50.0	15.24
CCF59B-100	100.0	30.48

NOTES:

CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.

CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY C.MCCORMICK	01/29/2004	
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005	CHECKED BY D.PARHAM	01/29/2004	PRODUCT DESCRIPTION CA F M/F M RG59B/U
PROJECTION 	APPROVED BY R.CARRICK	01/29/2004	
	SIZE A	FSCM NO. 43321	DWG. NO. CCF59B
	SCALE: NONE	CAD FILE: CCF59B.SLDDRW	REV. D
			SHEET 1 OF 1