


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED FOR PRODUCTION	8/21/01	MCCORMICK
B	ECN 3277: UPDATE DWG FORMAT	4/11/08	D.GRIFFIN
C	ECN 4702: CN RELEASE AND NEW FORMAT	4/23/10	D.FRISIELLO



MODEL #	LENGTH	
	FEET	METERS
CCF6-1	1.0	0.31
CCF6-3	3.0	0.92
CCF6-6	6.0	1.83
CCF6-9	9.0	2.74
CCF6-12	12.0	3.66
CCF6-25	25.0	7.63
CCF6-50	50.0	15.25
CCF6-100	100.0	30.49

NOTES:
 CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005	APPROVALS DRAWN BY MCCORMICK CHECKED BY ENG APPROVED BY D.PARHAM	DATE 08/21/01 08/21/01 08/27/01	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			CATEGORY COAXIAL
	PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
			DWG. NO. CCF6	REV. C
		SCALE: NONE	CAD FILE: CCF6.SLDDRW	
		SHEET 1 OF 1		