


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 8011: CHANGED CABLE TO LIGHT GRAY	7/9/15	D. CASTRO
F	ECN 8241: RELEASED TO SUZHOU, NEW MOLD TOOL	2/2/16	S.LI
G	ECN 8321: REVISED STRAIN RELIEF BOOTS	5/3/16	D.FRISIELLO
H	ECN 8363: REVISED LENGTH CHART TO BE GENERIC CHART	6/8/16	D.FRISIELLO



LENGTH CODE CHART		
CABLE # & LENGTH	LENGTH SYMBOL	EXAMPLE OF PART # USED
CCTN58-XXHRB	WHERE XX = LENGTH IN FEET	CCTN58-5HRB (5 FEET)

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		50 HIGH STREET NORTH ANDOVER, MA 01845
	DRAWN BY MCCORMICK	06/18/01		CATEGORY
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ±.005 [1.13]	CHECKED BY D.PARHAM	07/02/01	PRODUCT DESCRIPTION	
PROJECTION 	APPROVED BY ENG	07/05/01	CA BNC M/BNC M RA RG58/U	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE A	FSCM NO. 43321
	COLOR VARIATIONS MAY OCCUR		DWG. NO. CCTN58-HRB	REV. H
			SCALE: NONE	CAD FILE: CCTN58-HRB.SLDDRW
				SHEET 1 OF 1

8 7 6 5 4 3 2 1

D

C

B

A

D

C

B

A

8 7 6 5 4 3 2 1