


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 6951: REVISED L-COM LOGO, NEW FORMAT, PACKAGING NOTE, ROHS	7/11/13	D.FRISIELLO
F	ECN 7237: ADDED CHD15MM-1, UPDATED REGULATORY	1/14/14	D. CASTRO



WIRING MAP		
"P1"	WIRE COLOR	"P2"
1	BLACK	1
2	BROWN	2
3	RED	3
4	ORANGE	4
5	YELLOW	5
6	GREEN	6
7	BLUE	7
8	PURPLE	8
9	GRAY	9
10	WHITE	10
11	PINK	11
12	LIGHT GREEN	12
13	BLACK/WHITE	13
14	BROWN/WHITE	14
15	RED/WHITE	15
SHELL	DRAIN WIRE	SHELL

MODEL NUMBER	LENGTH	
	FEET	METERS
CHD15MM-1	1.0	.31
CHD15MM-2.5	2.5	.76
CHD15MM-5	5.0	1.52
CHD15MM-7.5	7.5	2.29
CHD15MM-10	10.0	3.05
CHD15MM-15	15.0	4.57
CHD15MM-25	25.0	7.62

NOTES:

INTERNAL 360° FOIL SHIELDS IN CONNECTOR HOODS CONNECTED TO CABLE DRAIN WIRE AND CONNECTOR FRAMES.

CONNECTOR PINS: GOLD PLATED.

CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.

CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [5.1] .XXX = ±.005 [1.3]	APPROVALS DRAWN BY: TJC CHECKED BY: DFP APPROVED BY: RC	DATE 8/8/01 8/15/01 8/16/01	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY D-SUBMINIATURE
	PROJECTION 		PRODUCT DESCRIPTION CA, HD15 MALE TO MALE
	COLOR VARIATIONS MAY OCCUR CHD-FS01	SIZE A FSCM NO. 43321 DWG. NO. CHD15MM REV. F	SCALE: NONE CAD FILE: CHD15MM.SLDDRW SHEET 1 OF 1