


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS | | | |
|-----------|-----------------|-----------|-------------|
| REV | DESCRIPTION | DATE | APPROVED |
| A | INITIAL RELEASE | 6/16/2022 | DGUTTADAURO |
| | | | |
| | | | |




| WIRING CHART | | | |
|--------------|----|---------|--------------|
| 1 | 1 | WHITE | POWER L +12V |
| 14 | 14 | 1 | INNER SHIELD |
| 2 | 25 | WHITE | Tx DATA 0- |
| 15 | 12 | RED | Tx DATA 0+ |
| 3 | 24 | WHITE | Tx DATA 1- |
| 16 | 11 | BLUE | Tx DATA 1+ |
| 4 | 23 | WHITE | Tx DATA 2- |
| 17 | 10 | GREEN | Tx DATA 2+ |
| 5 | 22 | WHITE | XCLK- |
| 18 | 9 | YELLOW | XCLK+ |
| 6 | 21 | WHITE | Tx DATA 3- |
| 19 | 8 | VIOLET | Tx DATA 3+ |
| 7 | 20 | RED | SerTC+ |
| 20 | 7 | BLACK | SerTC- |
| 8 | 19 | BLACK | SerTFG- |
| 21 | 6 | BLUE | SerTFG+ |
| 9 | 18 | BLACK | CC1- |
| 22 | 5 | GREEN | CC1+ |
| 10 | 17 | YELLOW | CC2+ |
| 23 | 4 | BLACK | CC2- |
| 11 | 16 | BLACK | CC3- |
| 24 | 3 | VIOLET | CC3+ |
| 12 | 15 | WHITE | CC4+ |
| 25 | 2 | BLACK | CC4- |
| 13 | 13 | 2 | INNER SHIELD |
| 26 | 26 | BLACK | POWER L +12V |
| | | HOUSING | OUTER SHIELD |

| PART NUMBER | LENGTH | |
|-------------|--------|--------|
| | FEET | METERS |
| CLCA01-1M | 3.28 | 1.0 |
| CLCA01-3M | 9.84 | 3.0 |
| CLCA01-5M | 16.4 | 5.0 |

- NOTES:
- CABLE SHALL BE TESTED FOR CONTINUITY.
 - CABLE SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

| | | | | | |
|--|----------------------------|---|---|------------------------------------|------------------|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [5] ANGLES ± 1° .XXX = ± .005 [13] | APPROVALS | DATE |  50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936 | | |
| | DRAWN BY DMAY | 6/16/2022 | | CATEGORY AUDIO/VIDEO | |
| | CHECKED BY DFRISIELLO | 6/17/2022 | | | |
| APPROVED BY DGUTTADAURO | 6/17/2022 | PRODUCT DESCRIPTION CAMERA LINK CABLE ASSEMBLY, MDR/MDR, PVC, IV | | | |
| THIRD-ANGLE PROJECTION | COLOR VARIATIONS MAY OCCUR | SIZE A | CAGE CODE 43321 | ITEM NO. CLCA01 | REV. A |
| | | SCALE: NONE | | CAD FILE: CLCA01.SLDDRW | |