


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISION | | | | | |
|----------|------|-----------------|------------|------------|-------------|
| ZONE | REV. | DESCRIPTION | DATE | CHANGED BY | APPROVED BY |
| | A | INITIAL RELEASE | 01/16/2023 | HBAKKE | GUTTADAURO |





| Pin | Wire | Color | Function |
|-----|------|---------|--------------|
| 1 | 1 | BLACK | POWER L +12V |
| 14 | 14 | 1 | INNER SHIELD |
| 2 | 25 | WHITE | Tx DATA 0- |
| 15 | 12 | RED | Tx DATA 0+ |
| 3 | 24 | WHITE | Tx DATA 1- |
| 16 | 11 | BLUE | Tx DATA 1+ |
| 4 | 23 | WHITE | Tx DATA 2- |
| 17 | 10 | GREEN | Tx DATA 2+ |
| 5 | 22 | WHITE | XCLK- |
| 18 | 9 | YELLOW | XCLK+ |
| 6 | 21 | WHITE | Tx DATA 3- |
| 19 | 8 | VIOLET | Tx DATA 3+ |
| 7 | 20 | RED | SerTC+ |
| 20 | 7 | BLACK | SerTC- |
| 8 | 19 | BLACK | SerTFG- |
| 21 | 6 | BLUE | SerTFG+ |
| 9 | 18 | BLACK | CC1- |
| 22 | 5 | GREEN | CC1+ |
| 10 | 17 | YELLOW | CC2+ |
| 23 | 4 | BLACK | CC2- |
| 11 | 16 | BLACK | CC3- |
| 24 | 3 | VIOLET | CC3+ |
| 12 | 15 | WHITE | CC4+ |
| 25 | 2 | BLACK | CC4- |
| 13 | 13 | 2 | INNER SHIELD |
| 26 | 26 | WHITE | POWER L +12V |
| | | HOUSING | OUTER SHIELD |

UL20276 11 TWIST PAIR 30AWG STRANDED TINNED COPPER
 2 CONDUCTOR 28AWG (UNINSULATED) PLUS
 2 CONDUCTOR 28AWG
 JACKET: PVC, GRAY

| PART NUMBER | LENGTH | |
|-------------|--------|--------|
| | FEET | METERS |
| CLCA03HF-1M | 3.28 | 1.0 |
| CLCA03HF-3M | 9.84 | 3.0 |
| CLCA03HF-5M | 16.40 | 5.0 |
| CLCA03HF-8M | 26.25 | 8.0 |

- NOTES:
- CABLE SHALL BE TESTED FOR CONTINUITY.
 - CABLE SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
 - FLEX RATED FOR 1,000,000 CYCLES.

REGULATORY COMPLIANCE:
 EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

| | | | | |
|--|---|--|---|--------------------------------|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13] | APPROVALS DRAWN BY HBAKKE CHECKED BY DMAY APPROVED BY GUTTADAURO | DATE 01/16/2023 01/16/2023 01/16/2023 |  an INFINIT® brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936 | |
| | THIRD-ANGLE PROJECTION  | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR | PRODUCT DESCRIPTION Camera Link Machine Vision High Flex Cable Assembly, PoCL, SDR26 male to SDR26 male, UL20276 PVC, Gray | CATEGORY AUDIO/VIDEO |
| SIZE A | | CAGE CODE 43321 | ITEM NO. CLCA03HF | REV. A |
| SCALE: NONE | | CAD FILE: clca03hf.SLDDRW | | SHEET 1 OF 1 |