

SARGENT

ROSTRA TOOL COMPANY > 30 EAST INDUSTRIAL ROAD > BRANFORD, CT 06405 USA CALL US: 203 488-8665

[home](#) | [about us](#) | [contact us](#) | [support library](#) | [downloads](#)

Select a family of tools



APPLICATIONS

[CATV/Satellite](#) >

[Electrical/
Electronic](#) >

[Plumbing Tools](#) >

[Industrial](#) >

[Telcom/Voice
/Data](#) >

[Historical](#) >

SERVICES

[Engineering](#) >

[Short Run
Production](#) >

[Private Label
Programs](#) >

SEARCH

[Part Number](#)



[Home](#) > [O.E.M. Compatible Crimp Tools](#) > **3127 CT**

U.S. dealers:

Choose-->



International dealers:

Choose-->



3127 CT

*Please note: If a distributor does not maintain stock on a particular item they may order it for you.

- Crimps D-subminiature pins and sockets (Ref:AMP 90312)
- The conductor and insulation crimps conform to O.E.M. specifications and are produced on one tool closure.
- Conductor crimps are "b" type, insulated crimps are "Oval" which are produced in two cavities: 28-24 AWG and 24-20 AWG.
- An easy load locator and wire stop are provided to orient the pins or sockets during crimping.

| Die Only: | Item Application: |
|-----------|-------------------|
|-----------|-------------------|

N/A

D-subminiature pins & sockets

| Connector/Terminal Type: | Cable/Crimp Type: | Crimp/HEX/Wire Sizes: | Strip Type/Dimensions: |
|--------------------------|-------------------|-----------------------|------------------------|
|--------------------------|-------------------|-----------------------|------------------------|

D-subminiature pins & sockets Ref: AMP 90312

Conductor crimp -"B" type, Insulation crimp -"Oval" type, 2 cavities

28-24 AWG

N/A

| Product Length: | Product Weight: |
|-----------------|-----------------|
|-----------------|-----------------|

9 inches

22.86 cm

15 ounces

.42 kgs

See more O.E.M. Compatible Crimp Tools:

Choose-->

