



an INFINIT® brand



Electrical Cabinet MINI-CAB Outdoor Single-phase 120 Vac 1x 40A + 1x 20A Tandem Branches UL 67 SASD

Cabinets Technical Data Sheet

CPD05-N140A

Features

- UL67
- Several Breaker Combinations Available
- Compact Form Factor
- Integral Surge Protection
- Wall Mount

Applications

- Small Cells
- 5G Sites
- DAS Systems
- Electrical Main Panels
- Electrical Sub-Panels
- Load Expansion

Description

Electrical cabinet (also known as power distribution box) CPD05-N140A from L-Com is a UL67 power distribution box that accepts a 120 Vac Single-phase electrical service and distributes power to individual loads via 1x 40A + 1x Tandem 20A circuit breakers. This electrical cabinet is equipped with a state-of-the-art SASD surge protector that provides lightning protection for downstream equipment to support long-term system reliability. L-Com electrical cabinets are available in stock with same day shipping.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Service Voltage		120		Vac
Maximum Continuous Operating Voltage (MCOV)				
L - N			150	Vac
Service Current Rating			60	A
Branch Breaker Rating		1x 40A + 1x Tandem 20A		A
Breaker Type		QO		

Surge Protection Specification

Description	Minimum	Typical	Maximum	Units
Surge Protection Technology		SASD		
Protection Modes		L-N		
8/20µs Surge Current			10	kA
Nominal Discharge Current Rating (In)		5		kA
VPR 8/20µs				
L - N			330	Vpk
SCCR (Short Circuit Current Rating)		10		kAIC

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Electrical Cabinet MINI-CAB Outdoor Single-phase 120 Vac 1x 40A + 1x 20A Tandem Branches UL 67 SASD CPD05-N140A](#)



an INFINIT® brand



Electrical Cabinet MINI-CAB Outdoor Single-phase 120 Vac 1x 40A + 1x 20A Tandem Branches UL 67 SASD

Cabinets Technical Data Sheet

CPD05-N140A

Mechanical Specifications

Size

Outer Height	10.2in	[259.08 mm]
Outer Width	5.3 in	[134.62 mm]
Outer Depth	4.3 in	[109.22mm]
Weight	6 lbs	[2.72 kg]
Enclosure Material and Plating	16 Gauge Steel	

Installation

Mount Type	Wall Mount
Service Wiring Terminals	Compression Lug
	Copper #14 AWG to #4 AWG
	Aluminum #12 AWG to #3 AWG
Status Indication Terminals	3-Position Screw Terminal #22 AWG to #16 AWG

Environmental Specifications

Temperature (Operating Range)	-20 to +65 deg C
Temperature (Storage Range)	-20 to +65 deg C
NEMA Rating	3R
Humidity	90% non-condensing

Compliance Certifications

UL Listed	UL 67 Listed, UL 1449 4th Ed
-----------	------------------------------

Our portfolio includes cable assemblies, connectors, adapters and custom products, as well as their wireless product line which includes antennas, RF amplifiers, coaxial lightning and surge protectors, and NEMA rated enclosures.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Electrical Cabinet MINI-CAB Outdoor Single-phase 120 Vac 1x 40A + 1x 20A Tandem Branches UL 67 SASD CPD05-N140A](https://www.l-com.com/Electrical%20Cabinet%20MINI-CAB%20Outdoor%20Single-phase%20120%20Vac%201x%2040A%20+%201x%2020A%20Tandem%20Branches%20UL%2067%20SASD%20CPD05-N140A)

URL: [https://www.l-com.com/Electrical Cabinet MINI-CAB Outdoor Single-phase 120 Vac 1x 40A + 1x 20A Tandem Branches UL 67 SASD-p.aspx](https://www.l-com.com/Electrical%20Cabinet%20MINI-CAB%20Outdoor%20Single-phase%20120%20Vac%201x%2040A%20+%201x%2020A%20Tandem%20Branches%20UL%2067%20SASD-p.aspx)

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume any liability arising out of the use of any part or documentation.

CPD05-N140A CAD Drawing

Electrical Cabinet MINI-CAB Outdoor Single-phase 120 Vac
1x 40A + 1x 20A Tandem Branches UL 67 SASD

