



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
D	ECN 3779: DEFINED COLOR TO LIGHT GRAY, NEW FORMAT	1/6/09	D.FRISIELLO
E	ECN 6692: ADDED NOTES, REVISED FORWARD, LOGOS, COLOR	1/14/13	D.FRISIELLO
F	ECN 7241: ADDED 1 & 25 FT LENGTHS, REVISED ROHS AND FORMAT	1/21/14	D.FRISIELLO



SUPPLIED WITH THUMBSCREWS IN PLACE
 NOTE: SUPPLIED WITH OPTIONAL USE HARDWARE AND INSTRUCTIONS
 CABLE INTERCONNECTION HARDWARE: (4) SCREWLOCKS, H= .191"
 PANEL MOUNT HARDWARE: (4) SCREWLOCKS, H= .160"

WIRING MAP		
"P1"	WIRE COLOR	"P2"
1	BLACK	1
2	BROWN	2
3	RED	3
4	ORANGE	4
5	YELLOW	5
6	GREEN	6
7	BLUE	7
8	PURPLE	8
9	GRAY	9
10	WHITE	10
11	PINK	11
12	LIGHT GREEN	12
13	BLACK / WHITE	13
14	BROWN / WHITE	14
15	RED / WHITE	15
SHELL	DRAIN WIRE	SHELL

PART NUMBER	LENGTH	
	FEET	METERS
CRMN15MM-1	1.0	.31
CRMN15MM-2.5	2.5	.76
CRMN15MM-5	5.0	1.52
CRMN15MM-10	10.0	3.05
CRMN15MM-15	15.0	4.57
CRMN15MM-25	25.0	7.62

- NOTES:**
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
 CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (mm)		APPROVALS		DATE	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845								
OVERALL CABLE LENGTH TOLERANCE: ≤12 (305) ±.01 (25) / -0 >12 (305) ≤60 (1524) ±.015 (1) / -0 >60 (1524) ≤120 (3048) ±.02 (508) ±.01 (25) / -0 >120 (3048) ≤300 (7620) ±.03 (762) ±.015 (1) / -0 >300 (7620) ±.05 (127) / -0		DRAWN BY T. CLARK		3/10/2004		CATEGORY D-SUBMINIATURE							
ALL OTHER DIMENSIONAL TOLERANCES: X = ±.2 (5.08) XX = ±.02 (51) XXX = ±.005 (127)		CHECKED BY D. PARHAM		3/30/2004	PRODUCT DESCRIPTION CABLE, DB25M/M REVERSIBLE HDWR								
PROJECTION 		APPROVED BY C. MCCORMICK		3/31/2004	<table border="1"> <tr> <td>SIZE</td> <td>FSCM NO.</td> <td>DWG. NO.</td> <td>REV.</td> </tr> <tr> <td>B</td> <td>43321</td> <td>CRMN15MM</td> <td>F</td> </tr> </table>	SIZE	FSCM NO.	DWG. NO.	REV.	B	43321	CRMN15MM	F
SIZE	FSCM NO.	DWG. NO.	REV.										
B	43321	CRMN15MM	F										
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		COLOR VARIATIONS MAY OCCUR		CRMN-FS01	SCALE: 1:1 CAD FILE: CRMN15MM.SDDRW SHEET 1 OF 1								