


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	1/15/09	D.GRIFFIN
B	ECN 4474: ADDED 1.0 FT LENGTH, UPDATED FORMAT, CHANGED NOTES	1/7/10	D. CASTRO
C	ECN4813: ADDED 26AWG & PANTONE 400C TO CABLE DESCRIPTION, ADDED LOGO NOTE	06/09/10	DFP
D	ECN 6902: REVISED L-COM LOGOS, CABLE DESCRIPTION, ADDED ROHS NOTE	6/17/13	D.FRISIELLO



WIRE CHART		
"P1"	COLOR	"J1"
1	BLACK	1
2	BROWN	2
3	RED	3
4	ORANGE	4
5	YELLOW	5
6	GREEN	6
7	BLUE	7
8	VIOLET	8
9	GRAY	9
10	WHITE	10
11	PINK	11
12	LIGHT GREEN	12
13	BLACK/WHITE	13
14	BROWN/WHITE	14
15	RED/WHITE	15
SHELL	DRAIN WIRE	SHELL

MODEL NUMBER	LENGTH	
	FEET	METERS
CS2N15MF-1	1.0	0.31
CS2N15MF-2.5	2.5	.76
CS2N15MF-5	5.0	1.52
CS2N15MF-10	10.0	3.05
CS2N15MF-15	15.0	4.57
CS2N15MF-25	25.0	7.62
CS2N15MF-50	50.0	15.24

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPEC. PS-0031.

REGULATORY COMPLIANCE:
ROHS, CE



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVALS DRAWN BY D.FRISIELLO CHECKED BY D.FORTIN APPROVED BY S.SMITH	DATE 12/15/08 12/15/08 12/15/08	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			CATEGORY D-SUBMINIATURE
	PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
	SCALE: NONE		DWG. NO. CS2N15MF	REV. D
CAD FILE: CS2N15MF.SLDRW			SHEET 1 OF 1	