


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	1/15/09	D.GRIFFIN
B	ECN 4474: ADDED 1.0 FT LENGTH, UPDATED FORMAT, ADDED NOTES	1/7/10	D. CASTRO
C	ECN4813: ADDED 26AWG & PANTONE 400C TO CABLE DESCRIPTION. ADDED LOGO NOTE.	06/09/10	DFP
D	ECN 6902: REVISED L-COM LOGOS, CABLE DESCRIPTION, ADDED ROHS NOTE	6/17/13	D.FRISIELLO



"P1"  
DB15 MALE  
CONNECTOR

"P2"  
DB15 MALE  
CONNECTOR

WIRE CHART		
"P1"	COLOR	"P2"
1	BLACK	1
2	BROWN	2
3	RED	3
4	ORANGE	4
5	YELLOW	5
6	GREEN	6
7	BLUE	7
8	VIOLET	8
9	GRAY	9
10	WHITE	10
11	PINK	11
12	LIGHT GREEN	12
13	BLACK/WHITE	13
14	BROWN/WHITE	14
15	RED/WHITE	15
SHELL	DRAIN WIRE	SHELL

MODEL NUMBER	LENGTH	
	FEET	METERS
CS2N15MM-1	1.0	0.31
CS2N15MM-2.5	2.5	.76
CS2N15MM-5	5.0	1.52
CS2N15MM-10	10.0	3.05
CS2N15MM-15	15.0	4.57
CS2N15MM-25	25.0	7.62
CS2N15MM-50	50.0	15.24

**NOTES:**

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPEC. PS-0031.



**REGULATORY COMPLIANCE:**  
ROHS, CE

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D.FRISIELLO	12/15/08		CATEGORY D-SUBMINIATURE
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY D.FORTIN	12/15/08	PRODUCT DESCRIPTION DB15 M/M PREMIUM MOLDED CABLE	
PROJECTION 	APPROVED BY S.SMITH	12/15/08	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	SIZE <b>A</b>
	COLOR VARIATIONS MAY OCCUR		FSCM NO. <b>43321</b>	DWG. NO. <b>CS2N15MM</b>
			SCALE: NONE	CAD FILE: CS2N15MM.SLDDRW
				SHEET 1 OF 1