

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVAL
A	DRAWING REPLACES CS4-OD1	6/27/14	D.FRISIELLO
B	ECN 11325: ADD PANTONE 424C TO JACKET SECTION	09/10/2021	D.GUST

MODEL	PRIMARY PACKAGING	SECONDARY PACKAGING	LENGTH
CS4-100	COIL	BOX	100.0 FEET
CS4-500	SPOOL	STRETCH WRAP	500.0 FEET
CS4-1K	SPOOL	STRETCH WRAP	1,000.0 FEET

CONDUCTOR SIZE: 24 AWG. (7/32) TINNED COPPER.



SHIELDING: ALUMINUM/MYLAR FOIL SHIELD AND 24 AWG. TINNED STRANDED COPPER DRAIN WIRE.

NOMINAL DIAMETER: 0.175 IN.

JACKET: CHROME GRAY PVC (PANTONE 424C). 

RATINGS: 300V, 80°C UL2464

COLOR CODE	
CONDUCTOR	COLOR
1	BLACK
2	WHITE
3	RED
4	GREEN

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] - 60 [1524] = +2 [51] / -0 >60 [1524] - 120 [3048] = +4 [102] / -0 >120 [3048] - 300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = .2 [5.08] .XX = .02 [.51] .XXX = .005 [.13]	APPROVALS	DATE	 50 HIGH STREET NORTH ANDOVER, MA 01845 an INFINITI® brand			
	DRAWN BY B.DAGGETT	7/14/00			CATEGORY	D-SUBMINIATURE
	CHECKED BY D.PARHAM	7/14/00	APPROVED BY R.CARRICK	7/14/00	PRODUCT DESCRIPTION 4 CONDUCTOR CABLE 24AWG GRY	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE A	FSCM NO. 43321	DWG. NO. CS4	REV. B
COLOR VARIATIONS MAY OCCUR		SCALE: 1:1	CAD FILE: CS4.SLDRW		SHEET 1 OF 1	