


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	CN INITIAL RELEASE	11/20/2013	B.ZHANG

PART NUMBER	LENGTH	
	FEET	METERS
CSMN4515-1MM-1	1	0.31
CSMN4515-1MM-2.5	2.5	0.76
CSMN4515-1MM-5	5	1.52
CSMN4515-1MM-10	10	3.05
CSMN4515-1MM-15	15	4.57
CSMN4515-1MM-25	25	7.62



WIRING MAP		
"P1"	WIRE COLOR	"P2"
1	BLACK	1
2	BROWN	2
3	RED	3
4	ORANGE	4
5	YELLOW	5
6	GREEN	6
7	BLUE	7
8	PURPLE	8
9	GRAY	9
10	WHITE	10
11	PINK	11
12	LIGHT GREEN	12
13	BLACK / WHITE	13
14	BROWN / WHITE	14
15	RED / WHITE	15
SHELL	DRAIN WIRE	SHELL

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPEC. PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005 PROJECTION 	APPROVALS B.ZHANG CHECKED BY F.MAO APPROVED BY T.LU	DATE 08/30/2013 11/20/2013 11/20/2013	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	CATEGORY D-SUBMINIATURE	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR				PRODUCT DESCRIPTION DELUXE MOLDED CBL, DB15 STR. M/DB15 45° TYPE1 M
	SIZE A	FSCM NO. 43321	DWG. NO. CSMN4515-1MM	REV. A	
	CSMN-FS01				