


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 3779: DEFINED COLOR TO LIGHT GRAY, NEW FORMAT	1/8/09	D.FRISIELLO
F	ECN 4474: ADDED 1.0 FT. LENGTH, UPDATED FORMAT, ADDED NOTES	1/7/10	D. CASTRO
G	ECN 6603: REVISED L-COM LOGO, ADDED COLOR	1/25/13	D.FRISIELLO



"P1"
2X, 9-PIN MALE
D-SUB CONNECTOR
GOLD PLATED PINS

L-COM LOGO
BOTH SIDES

UL STYLE 2464
9 CONDUCTOR CABLE
PVC JACKET, COLOR: LIGHT GRAY
(PANTONE 400C)

L-COM LOGO
BOTH SIDES

2X, MOLDED PVC STRAIN
RELIEF AND HOOD WITH
360° METAL FOIL SHIELD
COLOR: LIGHT GRAY
(PANTONE 400C)

"P2"

WIRING MAP		
"P1"	WIRE COLOR	"P2"
1	BLACK	1
2	GRAY	2
3	RED	3
4	GREEN	4
5	BROWN	5
6	BLUE	6
7	ORANGE	7
8	YELLOW	8
9	PURPLE	9
SHELL	DRAIN WIRE	SHELL

PART NUMBER	LENGTH	
	FEET	METERS
CSMN9MM-1	1.0	0.31
CSMN9MM-2.5	2.5	0.76
CSMN9MM-5	5.0	1.52
CSMN9MM-10	10.0	3.05
CSMN9MM-15	15.0	4.57
CSMN9MM-25	25.0	7.62
CSMN9MM-125	125.0	38.10

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPEC. PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVALS DRAWN BY TJC CHECKED BY DFP APPROVED BY CM	DATE 6/7/01 7/18/01 7/20/01	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			CATEGORY D-SUBMINIATURE
	PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	PRODUCT DESCRIPTION CABLE, DB9M/M MOLDED
	CSMN-FS01	SCALE: NONE	FSCM NO. 43321	DWG. NO. CSMN9MM
		CAD FILE: CSMN9MM.SLDDRW	SHEET 1 OF 1	