


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	CN RELEASE	2/25/08	D.GRIFFIN
B	ECN 4474; ADDED 1.0 FT LENGTH, UPDATED FORMAT, CHG'D NOTES, RoHS	1/7/10	D. CASTRO



WIRING MAP					
"P1"	COLOR	"P2"	"P1"	COLOR	"P2"
1	BLACK	1	14	BROWN/WHITE	14
2	BROWN	2	15	RED/WHITE	15
3	RED	3	16	ORANGE/WHITE	16
4	ORANGE	4	17	GREEN/WHITE	17
5	YELLOW	5	18	BLUE/WHITE	18
6	GREEN	6	19	PURPLE/WHITE	19
7	BLUE	7	20	RED/BLACK	20
8	PURPLE	8	21	ORANGE/BLACK	21
9	GRAY	9	22	YELLOW/BLACK	22
10	WHITE	10	23	GREEN/BLACK	23
11	PINK	11	24	GRAY/BLACK	24
12	LIGHT GREEN	12	25	PINK/BLACK	25
13	BLACK/WHITE	13	SHELL	DRAIN WIRE	SHELL

PART NUMBER	LENGTH	
	FEET	METERS
CSMNB25MM-1	1.0	0.31
CSMNB25MM-2.5	2.5	0.76
CSMNB25MM-5	5.0	1.52
CSMNB25MM-10	10.0	3.05
CSMNB25MM-15	15.0	4.57
CSMNB25MM-25	25.0	7.62
CSMNB25MM-50	50.0	15.24

NOTES:

- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPEC. PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D.FRISIELLO	2/22/08		CATEGORY D-SUBMINIATURE
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY D.FORTIN	2/22/08	PRODUCT DESCRIPTION CABLE, DB25M/M MOLDED BLK	
PROJECTION 	APPROVED BY S.SMITH	2/22/08	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	SCALE: NONE
	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. CSMNB25MM
			CAD FILE: CSMNB25MM.SLDDRW	SHEET 1 OF 1