



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS |  |          |             |
|-----------|--|----------|-------------|
| REV       | DESCRIPTION                                  | DATE     | CHANGED BY  |
| A         | INITIAL RELEASE                              | 12/18/13 | D.GRIFFIN   |
| B         | ECN 7284: REVISED "P1" CONNECTOR 180 DEGREES | 2/10/14  | D.FRISIELLO |



| WIRING MAP |               |       |
|------------|---------------|-------|
| "P1"       | COLOR         | "P2"  |
| 1          | BLACK         | 1     |
| 2          | BROWN         | 2     |
| 3          | RED           | 3     |
| 4          | ORANGE        | 4     |
| 5          | YELLOW        | 5     |
| 6          | GREEN         | 6     |
| 7          | BLUE          | 7     |
| 8          | PURPLE        | 8     |
| 9          | GRAY          | 9     |
| 10         | WHITE         | 10    |
| 11         | PINK          | 11    |
| 12         | LIGHT GREEN   | 12    |
| 13         | BLACK / WHITE | 13    |
| 14         | BROWN / WHITE | 14    |
| 15         | RED / WHITE   | 15    |
| SHELL      | DRAIN WIRE    | SHELL |



| MODEL NUMBER     | LENGTH FEET [METERS] |
|------------------|----------------------|
| CSMNRA15-2MM-1   | 1.0 [.31]            |
| CSMNRA15-2MM-2.5 | 2.5 [.76]            |
| CSMNRA15-2MM-5   | 5.0 [1.52]           |
| CSMNRA15-2MM-10  | 10.0 [3.05]          |
| CSMNRA15-2MM-15  | 15.0 [4.57]          |
| CSMNRA15-2MM-25  | 25.0 [7.62]          |

**NOTES:**

- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  
 OVERALL CABLE LENGTH TOLERANCE:  
 ≤12 [305] = +1 [25] / -0  
 >12 [305] ≤60 [1524] = +2 [51] / -0  
 >60 [1524] ≤120 [3048] = +4 [102] / -0  
 >120 [3048] ≤300 [7620] = +6 [152] / -0  
 >300 [7620] = +5% / -0%  
 ALL OTHER DIMENSIONAL TOLERANCES:  
 .X = ±.2 [5.08]  
 .XX = ±.02 [5.1]  
 .XXX = ±.005 [1.3]

| APPROVALS               | DATE    |
|-------------------------|---------|
| DRAWN BY<br>D.FRISIELLO | 9/19/13 |
| CHECKED BY<br>R.SCOTT   | 9/19/13 |
| APPROVED BY<br>S.SMITH  | 9/19/13 |

**L-com** Global Connectivity 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845

CATEGORY: D-SUBMINIATURE

PRODUCT DESCRIPTION: CA DB15M/M STR-RA EXIT 2

|          |              |              |          |
|----------|--------------|--------------|----------|
| SIZE     | FSCM NO.     | DWG. NO.     | REV.     |
| <b>B</b> | <b>43321</b> | CSMNRA15-2MM | <b>B</b> |

SCALE: 1:1 CAD FILE: CSMNRA15-2MM.SLDDRW SHEET 1 OF 1

