


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	12/17/13	D.GRIFFIN
B	ECN 7964: CHANGED L-COM LOGO TO "THIS SIDE ONLY"	5/27/15	D.FRISIELLO



WIRING MAP		
"P1"	COLOR	"P2"
1	BLACK	1
2	GRAY	2
3	RED	3
4	GREEN	4
5	BROWN	5
6	BLUE	6
7	ORANGE	7
8	YELLOW	8
9	PURPLE	9
SHELL	DRAIN WIRE	SHELL

MODEL NUMBER	LENGTH FEET [METERS]
CSMNRA9-3MM-1	1.0 [.31]
CSMNRA9-3MM-2.5	2.5 [.76]
CSMNRA9-3MM-5	5.0 [1.52]
CSMNRA9-3MM-10	10.0 [3.05]
CSMNRA9-3MM-15	15.0 [4.57]
CSMNRA9-3MM-25	25.0 [7.62]

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D.FRISIELLO	8/23/13		CATEGORY
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ± .005 [1.13]	CHECKED BY R.SCOTT	8/23/13	PRODUCT DESCRIPTION	
PROJECTION	APPROVED BY S.SMITH	8/23/13	CA DB9M/M STR-RA EXIT 3	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
	SCALE: NONE	CAD FILE: CSMNRA9-3MM.SLDRW	DWG. NO. CSMNRA9-3MM	REV. B
			SHEET 1 OF 1	