


**CSPL09 Bulk Cable Specification**



| ITEM                         | DESCRIPTION        |  |
|------------------------------|--------------------|--|
| Conductor                    | No. of Conductors  | 9                                      |
|                              | Material           | Tinned Copper                          |
|                              | Construction       | 24 AWG stranded (7 x 32)               |
| Insulation                   | Material           | Halar E-CTFE                           |
|                              | Nominal Thickness  | .006"                                  |
|                              | Nominal Diameter   | .034" to .038"                         |
| Shielding                    | Material           | Aluminum / Mylar                       |
|                              | Coverage           | 100%                                   |
|                              | Drain Wire         | 24 AWG stranded (7 x 32) tinned copper |
| Braiding                     | Material           | None                                   |
|                              | Coverage           | N/A                                    |
| Jacket                       | Material           | Halar E-CTFE                           |
|                              | Nominal Thickness  | .010"                                  |
|                              | Nominal Diameter   | .168"                                  |
|                              | Color              | Natural                                |
| Marking:                     |                    |  |
| <b>ELECTRICAL PROPERTIES</b> |                    |  |
| Temperature Range            | -40°C to 150°C     |  |
| Voltage                      | UL 300V Power Ltd. |  |
|                              |                    |  |
|                              |                    |  |