


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

| REVISIONS | | | |
|-----------|-----------------|--------|-----------|
| REV | DESCRIPTION | DATE | APPROVED |
| A | INITIAL RELEASE | 5/3/13 | D.GRIFFIN |
| | | | |
| | | | |



"P1"
2X MALE 9-PIN
D-SUB CONNECTOR

"P2"

| "P1" | WIRE COLOR | "P2" |
|-------|------------|-------|
| 1 | BLACK | 1 |
| 2 | RED | 2 |
| 3 | ORANGE | 3 |
| 4 | YELLOW | 4 |
| 5 | GREEN | 5 |
| 6 | BLUE | 6 |
| 7 | VIOLET | 7 |
| 8 | GRAY | 8 |
| 9 | BROWN | 9 |
| SHELL | DRAIN WIRE | SHELL |

| PART NUMBER | LENGTH | |
|-------------|--------|--------|
| | FT | METERS |
| CSPL9MM-2.5 | 2.5 | 0.76 |
| CSPL9MM-5 | 5.0 | 1.52 |
| CSPL9MM-10 | 10.0 | 3.05 |
| CSPL9MM-15 | 15.0 | 4.57 |
| CSPL9MM-25 | 25.0 | 7.62 |
| CSPL9MM-50 | 50.0 | 15.24 |

NOTES:

- CABLE: UL STYLE 2919, 9 CONDUCTOR (26AWG) (DOUBLE SHIELDED, BRAID & FOIL) JACKET: PVC, COLOR: LIGHT GRAY (PANTONE 400C)
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPEC. PS-0031.

| | | | | |
|---|--|----------------------------|--|--|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: $\leq 12 [305] = +1 [25] / -0$ >12 [305] $\leq 60 [1524] = +2 [51] / -0$ >60 [1524] $\leq 120 [3048] = +4 [102] / -0$ >120 [3048] $\leq 300 [7620] = +6 [152] / -0$ >300 [7620] = +3% / -0% | APPROVALS | DATE | | 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845 |
| | DRAWN BY D.PARHAM | 05/05/2011 | | CHECKED BY D.DESJARDIN |
| ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005 | APPROVED BY S.SMITH | 01/04/2013 | PRODUCT DESCRIPTION CA DB9M/M PLAS ARMR | |
| PROJECTION | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY | COLOR VARIATIONS MAY OCCUR | SIZE A | FSCM NO. 43321 |
| | | | DWG. NO. CSPL9MM | REV. A |
| | CS2N-FS01 | SCALE: NONE | CAD FILE: CSPL9MM.SLDDRW | SHEET 1 OF 1 |