

USB BULK CABLE SPECIFICATION

MODEL NO.	LENGTH
CSUSB-100	100 FEET
CSUSB-500	500 FEET
CSUSB-1000	1,000 FEET

<p style="text-align: center;">CROSS-SECTIONAL VIEW</p> <p>DRAIN WIRE JACKET BRAID FOIL SHIELD</p>	<p style="text-align: center;">COLOR CODE</p> <p>UNIT A 1. WHITE 2. GREEN</p> <p>UNIT B 3. RED 4. BLACK</p>
--	---

DESCRIPTION: USB CABLE REV 2.0

ITEM	UNIT A	UNIT B
CONSTRUCTION AWG	28 AWG - TWISTED PAIR	20 AWG
CONDUCTORS	CONDUCTOR SIZE, IN [MM]	7/.005±.0003 [.127±.008]
	MATERIAL	STRANDED TINNED COPPER
INSULATION	MATERIAL	POLYOLEFIN
	DIAMETER, IN [MM]	.031±.003 [.78±.08]
TAPE	MATERIAL	ALUMINUM MYLAR
	COVERAGE	125%
DRAIN WIRE	CONDUCTOR SIZE, IN [MM]	7/.005±.0003 [.127±.008] (28 AWG)
	MATERIAL	TINNED COPPER
BRAID SHIELD	MATERIAL	TINNED COPPER
	COVERAGE	65%
JACKET	MATERIAL	PVC
	DIAMETER, IN [MM]	.201±.006 [5.1±.15]
	COLOR	LIGHT GRAY (PANTONE 400)
MARKING	USB Revision 2.0 SHIELDED 28 AWG/2C+20 AWG/2C (UL) AWM2725 80°C 30V VW-1 [MANUFACTURER U.L. FILE ##] WWW.L-COM.COM	

ELECTRICAL PROPERTIES

ITEM	COMPONENT A	COMPONENT B
CONDUCTOR RESISTANCE	237 Ω/KM @ 68°F [20°C] MAX	34 Ω/KM @ 68°F [20°C] MAX
INSULATION RESISTANCE	300 MΩ-KM @ 68°F [20°C] MIN	100 MΩ-KM @ 68°F [20°C] MIN
DIELECTRIC STRENGTH	500 VAC/1 MIN	500 VAC/1 MIN
VOLTAGE RATING	30V	
TEMPERATURE RATING	176°F [80°]	