



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 6519: UPDATED FORMAT, NOTES/PACKAGING, AND LOGOS	11/19/12	D. DESJARDIN



MODEL NUMBER	LENGTH FEET [METERS]
CTL3B-5	5.0 [1.52]
CTL3B-7.5	7.5 [2.28]
CTL3B-10	10.0 [3.05]
CTL3B-15	15.0 [4.57]
CTL3B-25	25.0 [7.62]

- NOTES:
- CABLE SHALL BE TESTED FOR CONTINUITY.
  - CABLE SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%  ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVALS DRAWN BY RON CARRICK CHECKED BY ENG APPROVED BY C. MCCORMICK	DATE 9/17/2001 9/17/2001 9/17/2001	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY  COLOR VARIATIONS MAY OCCUR	
SIZE <b>A</b>		FSCM NO. <b>43321</b>	DWG. NO. <b>CTL3B-5</b>
SCALE: NONE		CAD FILE: CTL3B-5.SLDDRW	SHEET 1 OF 1