


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
C	ECN4924:CN RELEASE	23.JULY.2010	Bill_Zhang
D	ECN5142: ADD TOLERANCE MARK Δ	11/16/10	B.Zhang




16x 75 OHM BNC MALE (GOLD PLATING PIN)

UL STYLE 2919 EIGHT MINIATURE 75 OHM COAXIAL LINE COMPOSED OF COPPER SPIRAL SHIELD PLUS ALUMINUM MYLAR SHIELD OUTER JACKET: PVC, BLACK COLOR

L-com LOGO (BOTH SIDE)

16x MOLDED PVC HOOD AND STRAIN RELIEF, BLACK COLOR



MODEL NUMBER	LENGTH	
	FEET	METER
CTL8B-5B	5.0	1.52
CTL8B-7.5B	7.5	2.28
CTL8B-10B	10.0	3.05
CTL8B-15B	15.0	4.57
CTL8B-20B	20.0	6.10
CTL8B-25B	25.0	7.62

RoHS Compliant

- NOTES
1. CABLES TO BE TESTED FOR CONTINUITY
 2. CABLES TO BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-com PACKAGING SPEC PS-0031

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1[25] / -0 > 12 [305] ≤ 60 [1524] = +2[51] / -0 > 60 [1524] ≤ 120 [3048] = +4[102] / -0 > 120 [3048] ≤ 300 [7620] = +6[152] / -0 > 300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCE: .X = ± 2 [508] .XX = ± 0.2 [51] .XXX = ± 0.005 [13]	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY Bill_Zhang	05/28-'10		
	CHECKED BY D.CASTRO	07/23-'10	PRODUCT DESCRIPTION CA MULTI-COAX 8 BNC M-M	
	APPROVED BY D.PARHAM	07/23-'10		
SIZE A FSCM NO. 43321 DWG. NO. CTL8B-5B REV. D			SCALE: NONE CAD FILE: CTL8B-5B.SLDDRW SHEET 1 OF 1	