



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	1/25/10	D.GRIFFIN
B	ECN 6641: ADDED 1 FT LENGTH, REVISED LOGO	1/24/13	D.FRISIELLO



CABLE: UL 2919, THREE 75 OHM COAXIAL CONDUCTORS, FOUR TWISTED PAIRS, 26 AWG AND TWO CONDUCTORS 26 AWG, WITH ALUMINUM/POLYESTER FOIL SHIELD AND DRAIN WIRE PLUS TINNED COPPER BRAIDED WIRE. JACKET: PVC, BLACK



PART NUMBER	LENGTH	
	FEET	METERS
CTLF3VGAMF-1	1.0	.30
CTLF3VGAMF-3	3.0	.91
CTLF3VGAMF-5	5.0	1.52
CTLF3VGAMF-10	10.0	3.05
CTLF3VGAMF-20	20.0	6.09
CTLF3VGAMF-25	25.0	7.62
CTLF3VGAMF-50	50.0	15.24
CTLF3VGAMF-100	100.0	30.48
CTLF3VGAMF-200	200.0	60.96

- NOTES:**
1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D. CASTRO	1/25/10		CATEGORY
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY D. PARHAM	1/25/10		PRODUCT DESCRIPTION
PROJECTION	APPROVED BY P. MCNEIL	1/25/10		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY
	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. CTLF3VGAMF
		SCALE: NONE	CAD FILE: CTLF3VGAMF.SLDRW	SHEET 1 OF 1