

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVAL
A	DRAWING REPLACES DGBH1010K-OD1	8/19/14	D.FRISIELLO



SLIM LINE D-SUB GENDER CHANGERS



<u>Part Number</u>	<u>Description</u>	<u>Quantity</u>
DGBH15F	Female to Female HDB15	1
DGBH15M	Male to Male HDB15	1
DGBH26F	Female to Female HDB26	1
DGBH26M	Male to Male HDB26	1
DGBH44F	Female to Female HDB44	1
DGBH44M	Male to Male HDB44	1
DGBH62F	Female to Female HDB62	1
DGBH62M	Male to Male HDB62	1

NOTES:

ADAPTER KIT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

CE2011/65/EU(ROHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] - 60 [1524] = +2 [51] / -0 >60 [1524] - 120 [3048] = +4 [102] / -0 >120 [3048] - 300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = .2 [5.08] .XX = .02 [51] .XXX = .005 [13]	APPROVALS DRAWN BY MCCORMICK	DATE 3/1/02	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845				
	CHECKED BY D.PARHAM	3/1/02			CATEGORY D-SUBMINIATURE		
APPROVED BY R.CARRICK	3/1/02	PRODUCT DESCRIPTION ADPT, KIT HDB GNDR CHGR 8 PC					
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. DGBH1010K	REV. A
SCALE: 1:1		CAD FILE: DGBH1010K.SLDRW		SHEET 1 OF 1			