



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
A	RE-DRAWN FROM MAC TO NEW FORMAT	12/13/07	D.FRISIELLO



"P1"
MALE 25 CONTACT
D-SUB CONNECTOR



RECESSED SPACE FOR
LABEL, BOTH SIDES (.6" X 1.25")



"P2"
MALE 25 CONTACT
D-SUB CONNECTOR

NOTES:

MATERIAL:

HOUSING: STEEL (24 GA)
CONNECTOR SHELL: STEEL
INSULATOR: THERMOPLASTIC, UL94V-0 RATED
CONTACTS: PHOSPHOR BRONZE
HARDWARE: STEEL OR BRASS

FINISH:

HOUSING: BRIGHT NICKEL PLATED
CONNECTOR SHELL: TIN PLATED
CONTACTS: GOLD FLASH IN CONTACT AREA OVER NICKEL PLATE
HARDWARE: NICKEL PLATED

MISCELLANEOUS:

STEEL HOUSING PROVIDES COMPLETE 360° SHIELDING
OPERATING TEMPERATURE: -20°C TO +60°C
KIT TO BE INDIVIDUALLY PACKAGED IN A POLYBAG

JUMPER WIRES NOT INCLUDED. ORDER SEPARATELY
L-COM TD-JS, TD-JP, OR TD-JT TERMINATED JUMPER
WIRES FOR EASY PUSH-ON PROGRAMMING.

KIT INCLUDES

- 1 - 2 PIECE METAL HOUSING.
- 2 - MALE DB25 WITH PC TYPE TERMINALS.
- 4 - #4-40 JACK SCREWS WITH RETAINER CLIPS.

FORMALLY MAC 93-072301

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (mm) TOLERANCES TO BE: .X ±.1 [2.5] ANGLES ±2° .XX ±.01 [.25] .XXX ±.005 [.13] OVERALL CABLE LENGTH TOL: ≤ 60 [1524] +3 [76.2] / -0 > 60 [1524] +5% / -0%	APPROVALS	DATE
	DRAWN BY D.FRISIELLO	12/13/07
	CHECKED BY D.PARHAM	12/13/07
	APPROVED BY J.KIEZULAS	12/13/07
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	

	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CATEGORY	DATA CABLING
PRODUCT DESCRIPTION		
ADAPTER KIT, METAL, DB25 M/M		
SIZE A	FSCM NO. 43321	DWG. NO. DIYKS-M
SCALE: NONE CAD FILE: DIYKS-M.SLDDRW		REV. A