


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
A	RE-DRAWN FROM MAC TO NEW FORMAT	12/13/07	D.FRISIELLO



NOTES:

MATERIAL:

HOUSING: STEEL (24 GA)
 CONNECTOR SHELL: STEEL
 INSULATOR: THERMOPLASTIC, UL94V-0 RATED
 CONTACTS: PHOSPHOR BRONZE
 HARDWARE: STEEL OR BRASS

FINISH:

HOUSING: BRIGHT NICKEL PLATED
 CONNECTOR SHELL: TIN PLATED
 CONTACTS: GOLD FLASH IN CONTACT AREA OVER NICKEL PLATE
 HARDWARE: NICKEL PLATED

MISCELLANEOUS:

STEEL HOUSING PROVIDES COMPLETE 360° SHIELDING
 OPERATING TEMPERATURE: -20°C TO +60°C
 KIT TO BE INDIVIDUALLY PACKAGED IN A POLYBAG

JUMPER WIRES NOT INCLUDED. ORDER SEPARATELY
 L-COM TD-JS, TD-JP, OR TD-JT TERMINATED JUMPER
 WIRES FOR EASY PUSH-ON PROGRAMMING.

KIT INCLUDES

- 1 - 2 PIECE METAL HOUSING.
- 1 - FEMALE DB25 WITH PC TYPE TERMINALS AND FIXED #4-40 HEX STAND-OFF NUTS.
- 1 - MALE DB25 WITH PC TYPE TERMINALS.
- 2 - #4-40 JACK SCREWS WITH RETAINER CLIPS.

FORMALLY MAC 93-072301

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (mm) TOLERANCES TO BE: .X ±.1 [2.5] ANGLES ±2° .XX ±.01 [.25] .XXX ±.005 [.13] OVERALL CABLE LENGTH TOL: ≤ 60 [1524] +3 [76.2] / -0 > 60 [1524] +5% / -0%	APPROVALS	DATE
	DRAWN BY D.FRISIELLO	12/13/07
	CHECKED BY D.PARHAM	12/13/07
	APPROVED BY J.KIEZULAS	12/13/07
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	

	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CATEGORY DATA CABLING	
PRODUCT DESCRIPTION ADAPTER KITS, METAL DB25 M/F		
SIZE A	FSCM NO. 43321	DWG. NO. DIYKS
SCALE: NONE CAD FILE: DIYKS.SLDDRW		SHEET 1 OF 1