




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/10/11	D.GRIFFIN



DB25 FEMALE SOLDER CUP CONNECTOR



STEEL CASE, NICKEL PLATED.



DB25 MALE SOLDER CUP CONNECTOR

NOTES:

ALL DIMENSIONS ARE FOR REFERENCE ONLY.

KIT IS SUPPLIED UN-ASSEMBLED.

INTERCONNECTING WIRES NOT INCLUDED.

KIT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVALS DRAWN BY D.FRISIELLO	DATE 10/5/11		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	CHECKED BY C.BRAN	10/5/11		CATEGORY DATA CABLING
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	PRODUCT DESCRIPTION KIT, METAL DIY DB25 M/F	SHEET 1 OF 1
SCALE: NONE	CAD FILE: DIYS.SLDDRW	SIZE A	FSCM NO. 43321	DWG. NO. DIYS